



Sférická a kuželová podložka DIN 6319 C 87197

Číslo položky	87197AMF
Značka	-
UBB	500617975494
UNSPSC	31161801
EAN	4020772087197
PKG. of 1	Len kompletne balenie

Technické parametre

Info	F max = Maximum recommended static load (values do not apply to stainless steel) These spherical washers are often combined with conical seats to DIN 6319-D or DIN 6319-G. The combination enables a swing of approximately 3° in any direction to be attained, when positioning a bolt through. ATTENTION: When these washers are applied in combination with fasteners in class 10.9 or 10, the maximum allowable clamping load is at 46% of the yield strength $R_{p0,2}$ for fasteners in class 8.8 or 8 the maximum is at 66% of the yield strength $R_{p0,2}$ Do not apply conical seats to DIN 6319-D with slotted holes,
------	--

Normy

DIN	6319-C
-----	--------

but use conical seats
to DIN 6319-G for
this purpose

Technické špecifikácie

Technický náčrt

