

10X135T



Číslo položky	88786FIS
Značka	-
UBB	500616693346
UNSPSC	30171906
EAN	4006209887868
PKG. of 1	Len kompletne balenie

Technické parametre

ETA-Certifikát	Yes
DIBt schválení	Yes
Info	do = Nominal diameter of drill bit Min. td = Recommended drilling depth hef = Effective anchorage depth tfix = Grip range Allowable load (kN) for a single anchor for multiple fixings of non-structural applications in normal concret. For combinations of tensile loads, shear loads, bending moments as well as reduced edge distances or spacings (anchor groups) see approval.

Normy

Technické špecifikácie

Technický náčrt

FABORY

