

10X140T



Číslo položky	89188FIS
Značka	-
UBB	500616783766
UNSPSC	30171906
EAN	4006209891889
PKG. of 1	Len kompletne balenie

Technické parametre

Priemer	10 mm
Dĺžka	140 mm
Info	do = Nominal diameter of drill bit Min. td = Recommended drilling depth hef = Effective anchorage depth tdfix = Grip range Allowable load (kN) for a single anchor for multiple fixings of non-structural applications in normal concrete. For combinations of tensile loads, shear loads, bending moments as well as reduced edge distances or spacings (anchor groups) see approval.

Normy

Technické špecifikácie

Technický náčrt

FABORY

