



## Svorníky so 2 šesťhrannými maticami UNC ASTM A193/ A194 Oceľ Zinc bichromated Gr.B7 - Gr.2H 7/8X120 (4.3/4)

|               |                       |
|---------------|-----------------------|
| Číslo položky | PIMI3222120           |
| Značka        | -                     |
| UBB           |                       |
| UNSPSC        |                       |
| EAN           |                       |
| PKG. of 1     | Len kompletne balenie |

### Technické parametre

|                    |                  |
|--------------------|------------------|
| Priemer            | 7/8 Inch         |
| Dĺžka              | 120 mm           |
| Trieda             | Gr.B7 - Gr.2H    |
| Materiál           | Oceľ             |
| Vlastnosti povrchu | Zinc bichromated |

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Normy

ASTM A193/A194

### Technické špecifikácie

|        |     |
|--------|-----|
| L (mm) | 120 |
|--------|-----|

### Technický náčrt

FABORY

