



Strojná skrutka plochá zapustená UNC ASME B18.6.3 ASME B18.6.3 Nerezocel' A2 (AISI 304/18-8) #2-56X1/8

Číslo položky	U51300.008.0012
Značka	-
UBB	500625035240
UNSPSC	31161504
EAN	8715492970442
PKG. of 100	Len kompletne balenie

Technické parametre

Priemer	NO.2
Dĺžka	1/8 Inch
Vlastnosti nákrutky	Phillips
Tvar hlavy	So zapustenou hlavou
Materiál	Nerezocel'
Technický materiál	ASTM F837 304
Smer závit	Pravý
Závit	Unified National Coarse
Závitov na palec	56

Info

Screws with diameter $\leq$ No.5 and length $\leq$ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length $\leq$ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Normy

ASME	B18.6.3
------	---------

Technické špecifikácie

A (max.)	0.162
H (max.)	0.051
Čís. krížovej drážky	1

Technický náčrt

