

Hexagon head bolt DIN 931 Steel Plain 8.8 M5X40

Article number	01000.050.040
Brand	-
UBB	950351001553
UNSPSC	31161620
EAN	8715492006929
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	22
b (min.): $L \leq 125$ mm	16
d-D	M5
k	3.5
L (mm)	40
P	0.8
s	8

Technical Drawing

