

Hexagon head bolt DIN 931 Steel Plain 8.8 M5X60

Article number	01000.050.060
Brand	-
UBB	950351001975
UNSPSC	31161620
EAN	8715492006967
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	22
b (min.): $L \leq 125$ mm	16
d-D	M5
k	3.5
L (mm)	60
P	0.8
s	8

Technical Drawing

