

Hexagon head bolt DIN 931 Steel Plain 8.8 M6X55

Article number	01000.060.055
Brand	-
UBB	950351002544
UNSPSC	31161620
EAN	8715492007094
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	55
P	1
s	10

Technical Drawing

