

Hexagon head bolt DIN 931 Steel Plain 8.8 M7X60

Article number	01000.070.060
Brand	-
UBB	950351003534
UNSPSC	31161620
EAN	8715492007322
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M7
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	26
b (min.): $L \leq 125$ mm	20
d-D	M7
k	4.8
L (mm)	60
P	1
s	11

Technical Drawing

