

Hexagon head bolt DIN 931 Steel Plain 8.8 M8X50

Article number	01000.080.050
Brand	-
UBB	950351003955
UNSPSC	31161620
EAN	8715492007391
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	50
P	1.25
s	13

Technical Drawing

