

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X80

Article number	01000.100.080
Brand	-
UBB	950351006198
UNSPSC	31161620
EAN	8715492007698
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	80
P	1.5
s	17

Technical Drawing

