

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X150

Article number	01000.100.150
Brand	-
UBB	950351006925
UNSPSC	31161620
EAN	8715492007797
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	150 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ISO	4014
NEN	1555
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	150
P	1.5
s	17

Technical Drawing

