

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X110

Article number	01000.120.110
Brand	-
UBB	950351008335
UNSPSC	31161620
EAN	8715492008060
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NEN	1555
ASME	B18.2.3.1M
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	110
P	1.75
s	19

Technical Drawing

