

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X170

Article number	01000.120.170
Brand	-
UBB	950351903394
UNSPSC	31161620
EAN	8715492008121
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M12
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
DIN	931
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	170
P	1.75
s	19

Technical Drawing

