

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X55

Article number	01000.160.055
Brand	-
UBB	950351011388
UNSPSC	31161620
EAN	8715492008503
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NEN	1555
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	55
P	2
s	24

Technical Drawing

