

Hexagon head bolt DIN 931 Steel Plain 8.8 M18X240

Article number	01000.180.240
Brand	-
UBB	950351015009
UNSPSC	31161620
EAN	8715492009050
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M18
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	240
P	2.5
s	27

Technical Drawing

