

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X300

Article number	01000.200.300
Brand	-
UBB	950351017245
UNSPSC	31161620
EAN	8715492009425
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	300 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	300
P	2.5
s	30

Technical Drawing

