

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X190

Article number	01000.240.190
Brand	-
UBB	950351914938
UNSPSC	31161620
EAN	8715492009920
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
DIN	931
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	190
P	3
s	36

Technical Drawing

