

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X260

Article number	01000.240.260
Brand	-
UBB	950351021023
UNSPSC	31161620
EAN	8715492010001
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	260 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	260
P	3
s	36

Technical Drawing

