

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X160

Article number	01000.270.160
Brand	-
UBB	950351022849
UNSPSC	31161620
EAN	8715492010247
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M27
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	160
P	3
s	41

Technical Drawing

