

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X140

Article number	01000.300.140
Brand	-
UBB	950351024829
UNSPSC	31161620
EAN	8715492010506
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NEN	1555
NF	E25-112
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	140
P	3.5
s	46

Technical Drawing

