

Hexagon head bolt DIN 931 Steel Plain 8.8 M33X100

Article number	01000.330.100
Brand	-
UBB	950351026725
UNSPSC	31161620
EAN	8715492010773
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M33
Length	100 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	100
P	3.5
s	50

Technical Drawing

