




Flat countersunk square neck bolt with short square DIN ≈608 Steel Plain 8.8 M16X40

Article number	01036.160.040
Brand	-
UBB	500644987801
UNSPSC	31161612
EAN	8717077048430
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	40 mm
Class	8.8
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	≈608
-----	------

Technical Specification

b (min.)	38
d-D	M16
dk (max.)	32
L (mm)	40
P	2
fn (max.)	13.5
v (max.)	16.7

Technical Drawing

