



Hexagon fit bolt with long thread DIN 609 Steel Plain 8.8 M10X30X13,9

Article number	01040.100.030
Brand	-
UBB	950351991084
UNSPSC	31161620
EAN	8715492018069
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	609
-----	-----

Technical Specification

b:50mmL≤150mm	19.5
b (min.): L150mm	24.5
b:L≤50mm	17.5
d-D	M10
ds (k6)	11
k	6.4
L (mm)	30
Lg (max.)	13.9
P	1.5
s	16
Tolerance drill ø	H7

Technical Drawing

