



Hexagon head bolt MEF DIN 960 Steel Plain 8.8 M10X1,00X70

Article number	01061.100.070
Brand	-
UBB	950351131665
UNSPSC	31161620
EAN	8715492020567
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Standards

NEN	1555
ISO	8765
DIN	960
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	70
P	1
s	17

Technical Drawing

