



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M8X125

Article number	01200.080.125
Brand	-
UBB	500644998618
UNSPSC	31161620
EAN	8717077049512
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	125 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
NEN	1555
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	125
P	1.25
s	13

Technical Drawing

