



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M16X430

Article number	01200.160.430
Brand	-
UBB	500644628512
UNSPSC	31161620
EAN	8717077011748
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	430 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L \geq 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	430
P	2
s	24

Technical Drawing

