



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M24X75

Article number	01200.240.075
Brand	-
UBB	950351159146
UNSPSC	31161620
EAN	8715492027580
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	75
P	3
s	36

Technical Drawing

