

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M6X70

Article number	01220.060.070
Brand	-
UBB	952351904513
UNSPSC	31161620
EAN	8715492033147
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M6
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	70
P	1
s	10

Technical Drawing

