

Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 8.8 M10X200/ S=17

Article number	01220.100.200
Brand	-
UBB	952351904778
UNSPSC	31161620
EAN	8715492033680
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	200 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	200
P	1.5
s	17

Technical Drawing

