

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M16X160

Article number	01220.160.160
Brand	-
UBB	950351171596
UNSPSC	31161620
EAN	8715492034298
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1555
NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	160
P	2
s	24

Technical Drawing

