

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M24X260

Article number	01220.240.260
Brand	-
UBB	954351335904
UNSPSC	31161620
EAN	8715492035066
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	260 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	260
P	3
s	36

Technical Drawing

