

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M27X110

Article number	01220.270.110
Brand	-
UBB	954351333271
UNSPSC	31161620
EAN	8715492035127
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M27
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
NEN	1555
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	110
P	3
s	41

Technical Drawing

