

Hexagon head bolt DIN 931 Steel Zinc plated with thick Cr(III) passivation 8.8 M10X70

Article number	01221.100.070
Brand	-
UBB	500648083276
UNSPSC	31161620
EAN	8717077202252
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NF	E25-112
DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	70
P	1.5
s	17

Technical Drawing

