

Hexagon head bolt DIN 931 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M20X70

Article number	01226.200.070
Brand	-
UBB	500571905271
UNSPSC	31161620
EAN	8715494287937
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	70 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1555
NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	70
P	2.5
s	30

Technical Drawing

