



Hexagon head bolt MF ISO 8765 Steel Zinc plated yellow passivated 8.8 M16X1,50X65

Article number	01240.160.065
Brand	-
UBB	952351012689
UNSPSC	31161620
EAN	8715492039354
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	65 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
NEN	1555
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	65
P	1.5
s	24

Technical Drawing

