



Hexagon flange bolt DIN
6921 Steel Plain 8.8 M8X30

Article number	01255.080.030
Brand	-
UBB	500648931136
UNSPSC	31161620
EAN	8717077235151
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Specific features of hexagon bolts with flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

ASME	≈B18.2.3.4M
ISO	≈4162
DIN	6921
EN	≈1665

Technical Specification

b (min.)	22
d-D	M8

Technical Drawing

dc (max.)	18
k (max.)	8.1
L (mm)	30
P	1.25
s	13

