

## Hexagon nut DIN 934 Steel Zinc plated yellow passivated |8| M3

|                |               |
|----------------|---------------|
| Article number | 01320.030.001 |
| Brand          | -             |
| UBB            | 950355017589  |
| UNSPSC         | 31161727      |
| EAN            | 8715492042811 |
| PKG. of 250    | Full Box Only |

### Technical Parameters

|                   |                                  |
|-------------------|----------------------------------|
| Diameter          | M3                               |
| Class             | 8                                |
| Driving features  | Hexagon                          |
| Material          | Steel                            |
| Thread direction  | Right                            |
| Surface treatment | Zinc plated yellow<br>passivated |
| Thread            | Metric thread                    |

### Standards

|     |         |
|-----|---------|
| NEN | 1560    |
| DIN | 934     |
| NF  | E25-401 |

### Technical Specification

|     |     |
|-----|-----|
| d-D | M3  |
| m   | 2.4 |
| P   | 0.5 |
| s   | 5.5 |

### Technical Drawing

