

Hexagon nut DIN 934 Steel Zinc plated with thick Cr(III) passivation |8| M10

Article number	01325.100.001
Brand	-
UBB	500505356039
UNSPSC	31161727
EAN	8715494207935
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NEN	1560
DIN	934
NF	E25-401

Technical Specification

d-D	M10
m	8
P	1.5
s	17

Technical Drawing

