

## Hexagon nut DIN 934 Steel Zinc plated with thick Cr(III) passivation |8| M12

|                |               |
|----------------|---------------|
| Article number | 01325.120.001 |
| Brand          | -             |
| UBB            | 500505356112  |
| UNSPSC         | 31161727      |
| EAN            | 8715494207942 |
| PKG. of 1      | Full Box Only |

### Technical Parameters

|                   |                                             |
|-------------------|---------------------------------------------|
| Diameter          | M12                                         |
| Class             | 8                                           |
| Driving features  | Hexagon                                     |
| Material          | Steel                                       |
| Thread direction  | Right                                       |
| Surface treatment | Zinc plated with thick Cr(III+) passivation |
| Thread            | Metric thread                               |

### Standards

|     |         |
|-----|---------|
| DIN | 934     |
| NEN | 1560    |
| NF  | E25-401 |

### Technical Specification

|     |      |
|-----|------|
| d-D | M12  |
| m   | 10   |
| P   | 1.75 |
| s   | 19   |

### Technical Drawing

