

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M20X140



Article No.	01400.200.140
Brand	-
UBB	950351195108
UNSPSC	31161620
EAN	8715492409065
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	140
Class	8.8

Standards

NF	E25-112
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	52
b (min.): L>200mm	65
b (min.): L≤125mm	46
k	12.5
P	2.50
s	30

Technical Drawing

