

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M20X280



Article No.	01400.200.280
Brand	-
UBB	950351939372
UNSPSC	31161620
EAN	8715492409140
PKG. of 10	Full Box Only

### Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	280
Class	8.8

### Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	52
b (min.): $L > 200\text{mm}$	65
b (min.): $L \leq 125\text{mm}$	46
k	12.5
P	2.50
s	30

### Technical Drawing

