

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M24X110

Article number	01400.240.110
Brand	-
UBB	950351196767
UNSPSC	31161620
EAN	8715492409416
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M24
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

NF	E25-112
ISO	4014
ASME	B18.2.3.1M
DIN	931
NEN	1555

### Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	54
d-D	M24
k	15
L (mm)	110
P	3
s	36

