

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M24X160



Article No.	01400.240.160
Brand	-
UBB	950351940180
UNSPSC	31161620
EAN	8715492409461
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M24
Length (L) (mm)	160
Class	8.8

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	60
b (min.): $L > 200\text{mm}$	73
b (min.): $L \leq 125\text{mm}$	54
k	15
P	3
s	36

Technical Drawing

