

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M27X80

Article number	01400.270.080
Brand	-
UBB	950351197260
UNSPSC	31161620
EAN	8715492409577
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M27
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931
ISO	4014

### Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	60
d-D	M27
k	17
L (mm)	80
P	3
s	41

