

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M30X200



Article No.	01400.300.200
Brand	-
UBB	950351199084
UNSPSC	31161620
EAN	8715492409751
PKG. of 10	Full Box Only

### Technical Parameters

Diameter (d-D)	M30
Length (L) (mm)	200
Class	8.8

### Standards

ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	72
b (min.): $L > 200\text{mm}$	85
b (min.): $L \leq 125\text{mm}$	66
k	18.7
P	3.50
s	46

### Technical Drawing

