

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M16X280

Article number	01410.160.280
Brand	-
UBB	500644663089
UNSPSC	31161620
EAN	8717077015197
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M16
Length	280 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

NEN	1568
NF	E25-114
ASME	B18.2.3.1M
ISO	4017
DIN	933

Technical Specification

d-D	M16
k	10
L (mm)	280

Technical Drawing

P	2
s	24

