

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M20X130

Article number	01410.200.130
Brand	-
UBB	500644663402
UNSPSC	31161620
EAN	8717077015234
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

DIN	933
NEN	1568
NF	E25-114
ISO	4017
ASME	B18.2.3.1M

Technical Specification

d-D	M20
k	12.5
L (mm)	130

Technical Drawing

P	2.5
s	30

