

## Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M20X160

Article number	01410.200.160
Brand	-
UBB	500644663733
UNSPSC	31161620
EAN	8717077015265
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M20
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

NF	E25-114
ISO	4017
ASME	B18.2.3.1M
DIN	933
NEN	1568

### Technical Specification

d-D	M20
k	12.5
L (mm)	160

### Technical Drawing

P	2.5
s	30

