

Hexagon head screw ISO metric thread DIN 933 Steel Hot dip galvanized 8.8 M24X120

Article number	01410.240.120
Brand	-
UBB	500644663998
UNSPSC	31161620
EAN	8717077015289
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

DIN	933
ASME	B18.2.3.1M
NEN	1568
NF	E25-114
ISO	4017

Technical Specification

d-D	M24
k	15
L (mm)	120

Technical Drawing

P	3
s	36

